





Hose Leg and Length Measurements

E90




I.D.	Leg Length
0 - 12mm	63 x 63mm
13 - 57mm	102 x 102mm
58 - 100mm	127 x 127mm
101mm & above	152 x 152mm

E45




I.D.	Leg Length
0 - 12mm	63 x 63mm
13 - 57mm	102 x 102mm
58 - 100mm	127 x 127mm
101mm & above	152 x 152mm

E135



I.D.	Leg Length
0 - 12mm	63 x 63mm
13 - 57mm	102 x 102mm
58 - 100mm	127 x 127mm
101mm & above	152 x 152mm


E180



I.D.	Leg Length
16 - 22mm	76mm
25 - 45mm	102mm
51 - 70mm	127mm
76mm	140mm


Note Centre Line Distance = I.D. x 3

RE90



I.D.	Leg Length
0 - 12mm	63 x 63mm
13 - 57mm	102 x 102mm
58 - 100mm	127 x 127mm
101mm & above	152 x 152mm

RE45



I.D.	Leg Length
0 - 12mm	63 x 63mm
13 - 57mm	102 x 102mm
58 - 100mm	127 x 127mm
101mm & above	152 x 152mm